



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SLD405840WHJB SLD405840WHJB

Cooper Lighting Solutions

Catalog Number	SLD405840WHJB
Manufacturer	Cooper Lighting Solutions
Description	
Weight per unit	1.4 (lbs/each)
Product Category	Led Recessed Architectural & S

Features

amperage rating	100m
Ballast Type	N/A
Lamp Included	Yes
Lamp Type	LED
Material	Die-Cast Aluminum
Number of Lamps	N/A
Voltage Rating	120
Wattage	12.2

Material, Color, and Finish

Finish	white
Style	(blank)

Descriptions

Description	SLD405840WHJB
Product Type	4" Surface Led DWNLT, Ic, 840, J Box Only
Special Features	Ultra-low profile surface luminaire with downlighting distribution

Manufacturer Information

Brand	HALO
GTIN	00080083713943
Manufacturers Part Number	SLD405840WHJB
sub brand	SLD4xJB LED
UPC	080083713943

Taxonomies, Classifications, and Categories

Category Description	LED GENERAL PURPOSE LIGHTING
Type	SLD4 LED

Availability

Manufacturer Status	Inactive
Status	Inactive

Packaging

Carton	1
Weight Per each	1.35



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	lighting
Mounting	Flushmount
standard	cULus Listed;cULus Listed - Damp Location;cULus Listed - Wet Location;EMI/RFI per FCC 47CFR Part 15 B;Energy Star Certified;AIR-TITE (TM) Certified ASTM E283;California Title 24;IECC Compliant;RoHS Compliant;LM79 and/or LM80 Tested;Washington State Energy Code