



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SP13I Plastic Wallplate 1G Blank W/Out Line Iv

*Pass & Seymour/Legrand*

|                  |  |
|------------------|--|
| Catalog Number   | SP13I  |
| Manufacturer     | Pass & Seymour/Legrand   |
| Description      | Wall Plate, 1 Gang, 5 In, 0.070 In Thickness, Thermoplastic, Ivory, 0.07187 LB |
| Weight per unit  | 0.0768 (lbs/each)  |
| Product Category | Wall Plates & Covers   |

### Features

|                 |          |
|-----------------|----------|
| cutout          | Blank    |
| insulation      | Bare     |
| orientation     | Vertical |
| Wall Plate Type | Blank    |

### Dimensions and Weight

|      |    |
|------|----|
| Size | 5" |
|------|----|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | PLASTIC WALLPLATE 1G BLANK W/OUT LINE IV |
| extra long description | P&S SP13I PLATE PLASTIC 1G BLNK W/O      |
| Special Features       | Standard size plastic smooth wall plate  |

### Manufacturer Information

|                           |                  |
|---------------------------|------------------|
| Brand                     | Pass and Seymour |
| GTIN                      | 00785007681642   |
| Manufacturers Part Number | SP13I            |
| UPC                       | 785007681642     |

### Taxonomies, Classifications, and Categories

|                      |                    |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type                 | Wall Plate         |

### Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Package         | 200    |
| Weight Per each | 0.0768 |

### Uses, Certifications, and Standards

|          |                     |
|----------|---------------------|
| Mounting | WALL                |
| standard | UL, CSA, CSA, UL514 |