



Made in the USA Since 1946

EMT Couplings Set Screw Type

- For coupling two ends of electrical metallic tubing
- Steel, zinc plated *
- UL rated Concrete Tight when Taped

EMT Couplings - Set Screw (SS)

| Cat. # | Size | Unit Ctn | Std Pkg | WT/ 100 |
|--------|--------|----------|---------|---------|
| SS60US | 1/2" | 50 | 250 | 10 |
| SS61US | 3/4" | 25 | 125 | 15 |
| SS62US | 1" | 10 | 50 | 24 |
| SS63US | 1-1/4" | 5 | 25 | 44 |
| SS64US | 1-1/2" | 5 | 25 | 68 |
| SS65US | 2" | - | 20 | 90 |
| SS66US | 2-1/2" | - | 5 | 158 |
| SS67US | 3" | - | 3 | 217 |
| SS68US | 3-1/2" | - | 2 | 250 |
| SS69US | 4" | - | 2 | 283 |

* Fittings 2 1/2" & Larger May Be Steel or Malleable Iron

Dimensional Table

| Cat. # | A Length | B Diameter |
|--------|----------|------------|
| SS60US | 1.75 | .937 |
| SS61US | 2.13 | 1.125 |
| SS62US | 2.50 | 1.375 |
| SS63US | 3.25 | 1.687 |
| SS64US | 3.75 | 1.968 |
| SS65US | 4.0 | 2.406 |
| SS66US | 4.25 | 3.220 |
| SS67US | 4.50 | 3.840 |
| SS68US | 4.75 | 4.360 |
| SS69US | 5.00 | 4.860 |

SPEC-grade





Made in the USA Since 1946

EMT Couplings Set Screw Type

- For coupling two ends of electrical metallic tubing
- Steel, zinc plated *
- UL rated Concrete Tight when Taped

EMT Couplings - Set Screw (SS)

| Cat. # | Size | Unit Ctn | Std Pkg | WT/ 100 |
|--------|--------|----------|---------|---------|
| SS60US | 1/2" | 50 | 250 | 10 |
| SS61US | 3/4" | 25 | 125 | 15 |
| SS62US | 1" | 10 | 50 | 24 |
| SS63US | 1-1/4" | 5 | 25 | 44 |
| SS64US | 1-1/2" | 5 | 25 | 68 |
| SS65US | 2" | - | 20 | 90 |
| SS66US | 2-1/2" | - | 5 | 158 |
| SS67US | 3" | - | 3 | 217 |
| SS68US | 3-1/2" | - | 2 | 250 |
| SS69US | 4" | - | 2 | 283 |

* Fittings 2 1/2" & Larger May Be Steel or Malleable Iron

Dimensional Table

| Cat. # | A Length | B Diameter |
|--------|----------|------------|
| SS60US | 1.75 | .937 |
| SS61US | 2.13 | 1.125 |
| SS62US | 2.50 | 1.375 |
| SS63US | 3.25 | 1.687 |
| SS64US | 3.75 | 1.968 |
| SS65US | 4.0 | 2.406 |
| SS66US | 4.25 | 3.220 |
| SS67US | 4.50 | 3.840 |
| SS68US | 4.75 | 4.360 |
| SS69US | 5.00 | 4.860 |

SPEC-grade

