



SINGLE RECEPTACLE OPENINGS, ONE GANG, 302/304 STAINLESS STEEL

SS7 | Pass & Seymour

FEATURES & BENEFITS

Smooth Metal Wall Plate 1gang Single 302/304 Stainless Steel



- Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness.
- Brushed finish.
- This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.
- Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

SPECIFICATIONS

GENERAL INFO

Size: Standard Type: Single

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cURus: No

UN SPSC: 39121704

TECHNICAL INFORMATION

Material: 302/304 Stainless Steel

Capacity: 2-gang

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA Buy American Act Status: Buy American Act Compliant

