

Eaton STL61A433CH

Catalog Number: STL61A433CH

Eaton meter socket, Transformer rated socket, 20A, Under, Solid top, Six-jaw, Pre-wired test switch, 600 Vac

General specifications



Photo is representative

Product Name

Eaton meter socket

UPC

786685703411

Product Height

21.8 in

Product Weight

25 lb

Catalog Number

STL61A433CH

Product Length/Depth

5.3 in

Product Width

12.6 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Catalog Notes

Austin Energy Approved, transformer rated

Product specifications

Type

Transformer rated socket

Amperage Rating

20A

Feed type

Bottom

Number of jaws

Six-jaw

Voltage rating

600 V

Accessories

Pre-wired test switch

Number of sockets

1

Resources

Specifications and datasheets

[Eaton Specification Sheet - STL61A433CH](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton STL61A433CH

Catalog Number: STL61A433CH

Eaton meter socket, Transformer rated socket, 20A, Under, Solid top, Six-jaw, Pre-wired test switch, 600 Vac

General specifications



Photo is representative

Product Name

Eaton meter socket

UPC

786685703411

Product Height

21.8 in

Product Weight

25 lb

Certifications

UL Listed

Catalog Number

STL61A433CH

Product Length/Depth

5.3 in

Product Width

12.6 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Catalog Notes

Austin Energy Approved, transformer rated

Product specifications

Type

Transformer rated socket

Amperage Rating

20A

Feed type

Bottom

Number of jaws

Six-jaw

Voltage rating

600 V

Accessories

Pre-wired test switch

Number of sockets

1

Resources

Specifications and datasheets

[Eaton Specification Sheet - STL61A433CH](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)