



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## **SU1500RTXLCDU Tripplete Ups System Su1500rtxlcd**

*Eaton Power Quality*

Catalog Number	SU1500RTXLCDU
Manufacturer	Eaton Power Quality
Description	Smartonline 1500VA 1350W 120V Double-Conversion Sine Wave Ups - 8 Outlets, Extended Run, Network Card Option, LCD, Usb, DB9, 2U Rack/Tower
Weight per unit	N/A
Product Category	20240322131518

### **Features**

amperage rating	1500 VA
charge time	3 hours recharge to 90%
Input Voltage	100V AC; 110V AC; 120V AC
Interface Type	(1) Contact closure; (1) RS-232; (1) Slot for SNMP/Web interface; (1) USB
media	Yes
nominal voltage	100V AC; 110V AC; 120V AC
Number of Outlets	(8) 5-15R
Outlet	NEMA 5-15P
Phase	Single-phase
Plug Type	5-15P
Voltage Rating	100V AC; 110V AC; 120V AC V
Wattage	1350 W

### **Dimensions and Weight**

Depth	17.720
Height	3.410 IN
Width	17.330 IN



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	TRIPLOTE UPS SYSTEM SU1500RTLCDU
extra long description	TRIPP SU1500RTLCD2U SU1500RTLCD2U
Features	The Tripp Lite series SmartOnline UPS lineup provides network-grade power protection and battery backup for critical equipment. Available in rack/tower, 1U rack, and tower form factors, this online double-conversion UPS delivers the highest level of power protection for networking, medical, automation, and light industrial equipment. Pure sine wave AC output and optional extended battery modules (where applicable) ensure the SmartOnline UPS provides advanced battery backup to keep sensitive equipment runni
Long Description	SmartOnline 1500VA 1350W 120V Double-Conversion Sine Wave UPS - 8 Outlets, Extended Run, Network Card Option, LCD, USB, DB9, 2U Rack/Tower
Product Type	Su1500rtxlcd2u
Special Features	1.5kVA 1.35kW 120V Battery Backup Protects Equipment against Damage, Downtime and Data LossThis on-line double-conversion UPS system maintains perfect output by converting AC input to DC, then reconverting UPS output to fully regulated sine wave AC. Constant on-line operation completely isolates sensitive equipment from every power problem on the AC line. The SmartOnline® SU1500RTLCD2U double-conversion UPS provides the highest level of power protection and battery backup for education, healthcare, milita

## Manufacturer Information

Brand	Eaton Power Quality
Manufacturers Part Number	SU1500RTLCD2U

## Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
----------------------	--------------------------

## Packaging

Carton	1
Weight	42.550 LB
Weight Per each	0

## Uses, Certifications, and Standards

Frequency Rating	50 / 60 Hz
Operating Temperature standard	32° to 104°F (0° to 40°C) ENERGY STAR Qualified; Meets FCC Part 15 Category A (EMI); ROHS (Restriction of Hazardous Substances); Tested to CSA (Canada); Tested to UL1778 (USA)
Temperature Rating	32° to 104°F (0° to 40°C)