



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SVX003A14A1B1 SVX9000 3HP 480V NEMA1 W/BR Chop Alfa PNL

Eaton Corp

Catalog Number	SVX003A14A1B1
Manufacturer	Eaton Corp
Description	Eaton SVX Adjustable Frequency Drive, Independent Drives, 3 HP, Nema Type 1/IP21, 480 V, FR4, Three-Phase, Emc H, Standard Software, A/N Keypad, Internal Brake Chopper, Standard Boards
Weight per unit	13.6 (lbs/each)
Product Category	Ac Drives

Features

keypad	Alphanumeric
--------	--------------

Dimensions and Weight

Depth	7.5
Height	9.6
Width	5

Descriptions

extra long description	ETN SVX003A1-4A1B1 SVX9000 3HP 480V
Features	Demand more accurate speed control. Eaton's SVX series of variable frequency drives offer sensorless vector control technology coupled with an adaptive motor model and sophisticated ASIC circuit features. This technology allows for steady speed error, fast torque rise time, high immunity to resonance vibrations and high starting torque and current. The SVX9000 is suitable for multiple motor drive systems and high-speed applications.
Long Description	Eaton SVX adjustable frequency drive, Independent Drives, 3 hp, NEMA Type 1/IP21, 480 V, FR4, Three-phase, EMC H, Standard Software, A/N keypad, Internal brake chopper, Standard boards
Product Type	SVX9000 3HP 480V N1 W/BR Chop Alfa PNL

Manufacturer Information

Brand	Eaton
GTIN	00782116011469
Manufacturers Part Number	SVX003A1-4A1B1
UPC	782116011469

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Adjustable frequency drive

Packaging

Carton	1
Weight Per each	13.55



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other

standard

EN 61800-3 Level H, IEC 61800-2, UL 508C, Contact Manufacturer