

Eaton SVX125A1-4A1N1

Catalog Number: SVX125A1-4A1N1

Eaton SVX adjustable frequency drive, 125HP, NEMA Type 1/IP21, 480V, FR8, Three-phase, EMC H, Standard Software, A/N keypad, No brake chopper, Standard boards



General specifications

| | |
|--------------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton SVX adjustable frequency drive | SVX125A1-4A1N1 |
| UPC | Product Length/Depth |
| 782116011599 | 13.5 in |
| Product Height | Product Width |
| 30.1 in | 11.5 in |
| Product Weight | Warranty |
| 127 lb | 2 year |
| Compliances | Certifications |
| Contact Manufacturer | IEC 61800-2 |
| | UL 508C |
| | EN 61800-3 Level H |

defaultTaxonomyAttributeLabel

Brake chopper

No brake chopper

Modification

Standard boards

Horsepower

125 hp

Frame size

8

Keypad

Alphanumeric

Input

EMC H

Three-phase

Rating

NEMA 1, IP21

Software

Standard

Resources

Application notes

[Electromagnetic compatibility \(EMC\)](#)

[Connecting drives to generator supplies](#)

[SPL - Variable frequency drives with a common DC bus](#)

Brochures

[SVX9000 Adjustable Frequency Drives Brochure](#)

[SVX9000 Adjustable Frequency Drives Product Aid](#)

Catalogs

[Eaton's Volume 6—Solid-State Motor Control](#)

[Product Datasheet - SVX125A1-4A1N1](#)

[Product Range Catalog Drives Engineering](#)

Drawings

[SVX_\(FR8\) 3D Inventor](#)

[SVX_\(FR8\) AutoCAD 2D Footprint \(mm\)](#)

[SVX_\(FR8\) 2D PDF](#)

[SVX_\(FR8\) 2D Drawing Xchange](#)

[SVX_\(FR8\) 3D Model Xchange](#)

[SVX and SPX Series FR4-FR11 PDF Open Drawings](#)

[SVX_\(FR8\) AutoCAD 2D Footprint](#)

Installation instructions

[9000X AFD User Manual](#)

Specifications and datasheets

[Eaton Specification Sheet - SVX125A1-4A1N1](#)

Eaton SVX125A1-4A1N1

Catalog Number: SVX125A1-4A1N1

Eaton SVX adjustable frequency drive, 125HP, NEMA Type 1/IP21, 480V, FR8, Three-phase, EMC H, Standard Software, A/N keypad, No brake chopper, Standard boards



General specifications

| | |
|--------------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton SVX adjustable frequency drive | SVX125A1-4A1N1 |
| UPC | Product Length/Depth |
| 782116011599 | 13.5 in |
| Product Height | Product Width |
| 30.1 in | 11.5 in |
| Product Weight | Warranty |
| 127 lb | 2 year |
| Compliances | Certifications |
| Contact Manufacturer | IEC 61800-2 |
| | UL 508C |
| | EN 61800-3 Level H |

defaultTaxonomyAttributeLabel

Brake chopper

No brake chopper

Modification

Standard boards

Horsepower

125 hp

Frame size

8

Keypad

Alphanumeric

Input

EMC H

Three-phase

Rating

NEMA 1, IP21

Software

Standard

Resources

Application notes

[Electromagnetic compatibility \(EMC\)](#)

[Connecting drives to generator supplies](#)

[SPL - Variable frequency drives with a common DC bus](#)

Brochures

[SVX9000 Adjustable Frequency Drives Brochure](#)

[SVX9000 Adjustable Frequency Drives Product Aid](#)

Catalogs

[Eaton's Volume 6—Solid-State Motor Control](#)

[Product Datasheet - SVX125A1-4A1N1](#)

[Product Range Catalog Drives Engineering](#)

Drawings

[SVX_\(FR8\) 3D Inventor](#)

[SVX_\(FR8\) AutoCAD 2D Footprint \(mm\)](#)

[SVX_\(FR8\) 2D PDF](#)

[SVX_\(FR8\) 2D Drawing Xchange](#)

[SVX_\(FR8\) 3D Model Xchange](#)

[SVX and SPX Series FR4-FR11 PDF Open Drawings](#)

[SVX_\(FR8\) AutoCAD 2D Footprint](#)

Installation instructions

[9000X AFD User Manual](#)

Specifications and datasheets

[Eaton Specification Sheet - SVX125A1-4A1N1](#)