Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



T10EM48 Emer T10 4FT 12/14/16W 30/35/40/50/65K

Rab Lighting

Catalog Number	T10EM48
Manufacturer	Rab Lighting
Description	Emergency Backup T10 4FT 12/14/16W 3000/3500/4000/5000/6500K
Weight per unit	1.0 (lbs/each)
Product Category	Lighting

Features

average life	50000
Base	T10 Linear
beam angle	140
Fixture Type	T10 tube with battery backup
lumens	500
total harmonic distortion	<20%
Voltage Rating	120-277
Wattage	16/14/12

Material, Color, and Finish

Color	White
color rendering index (cri)	=80
color temperature	3000/3500/4000/5000/6500
Finish	white

Dimensions and Weight

Length	51.97

Descriptions

Description	EMER T10 4FT 12/14/16W 30/35/40/50/65K
extra long description	RAB T10EM-48 EMER T10 4FT 12/14/16W
Long Description	EMERGENCY BACKUP T10 4FT 12/14/16W 3000/3500/4000/5000/6500K
Product Type	Emer T10 4FT 12/14/16W 30/35/40/50/65K
Special Features	CCT/Power Adjustable

Manufacturer Information

Brand	Rab Lighting
Manufacturers Part Number	T10EM-48

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	T10 Linear Emergency

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	1.04

Uses, Certifications, and Standards

Application	Indoor
standard	Meets NSF/ANSI standards for use in Food Zone (non-contact), Splash, and Non-Food Zones. Tube guard required in open fixtures.