



120 X 240 - 16/32
120 X 240 Primary Volts - 16/32 Secondary Volts - 1Ø
Buck-Boost Transformer - Single Phase

1083



Catalog #: T113074

PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R epoxy encapsulated
- Single or Three Phase Applications
- Wall Mounted
- Covered under Acme's 10 year limited warranty

BENEFITS

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in KVA

UL STANDARD

UL 506

CSA STANDARD

C22.2 No 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

| | |
|-----------------------|-----------|
| VA: | - |
| kVA: | 1.50 |
| Primary Voltage: | 120 X 240 |
| Secondary Voltage: | 16/32 |
| Frequency: | 60 Hz |
| Max Temperature Rise: | 115°C |
| UL Insulation Class: | 180°C |

PRODUCT MEASUREMENTS

| | |
|------------------|--------------|
| Height (In./cm): | 11.62 (29.5) |
| Width (In./cm): | 5.50 (14.0) |
| Depth (In./cm): | 5.13 (13.0) |

CONFIGURATION

| | |
|--------------------|--------------|
| Construction Type: | Encapsulated |
| Mounting Type: | Wall |

PACKAGING

| | |
|-----------------------|-----------|
| Ship Weight (Lbs/Kg): | 30 (13.6) |
|-----------------------|-----------|

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No 47
CSA Listed: LR7357-32
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf



120 X 240 - 16/32
120 X 240 Primary Volts - 16/32 Secondary Volts - 1Ø
Buck-Boost Transformer - Single Phase

1083



Catalog #: T113074

PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R epoxy encapsulated
- Single or Three Phase Applications
- Wall Mounted
- Covered under Acme's 10 year limited warranty

BENEFITS

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in KVA

UL STANDARD

UL 506

CSA STANDARD

C22.2 No 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

| | |
|-----------------------|-----------|
| VA: | - |
| kVA: | 1.50 |
| Primary Voltage: | 120 X 240 |
| Secondary Voltage: | 16/32 |
| Frequency: | 60 Hz |
| Max Temperature Rise: | 115°C |
| UL Insulation Class: | 180°C |

PRODUCT MEASUREMENTS

| | |
|------------------|--------------|
| Height (In./cm): | 11.62 (29.5) |
| Width (In./cm): | 5.50 (14.0) |
| Depth (In./cm): | 5.13 (13.0) |

CONFIGURATION

| | |
|--------------------|--------------|
| Construction Type: | Encapsulated |
| Mounting Type: | Wall |

PACKAGING

| | |
|-----------------------|-----------|
| Ship Weight (Lbs/Kg): | 30 (13.6) |
|-----------------------|-----------|

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No 47
CSA Listed: LR7357-32
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf