



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



T1M1UNV150P150L 150W Led PRGRM DRVR 500-1500MA CC

Fulham CO, Inc

Catalog Number	T1M1UNV150P150L
Manufacturer	Fulham CO, Inc
Description	Workhorse Led Extreme - Single Channel - 0-10V Dimming Led Driver - Universal Voltage Input - Programmable 500-1500MA Constant Current Output - 150W Max - Linear Case W/ End Terminals - Ip65
Weight per unit	2.3 (lbs/each)
Product Category	Led Emergency Drivers

Features

Input Current	1.4A Max
Lamp Type	LED
Minimum Starting Temperature	-40
Power Factor	> 0.9
total harmonic distortion	< 20%
Voltage Rating	120-277
Wattage	150

Dimensions and Weight

Height	1.52
Length	8.91
Width	2.33

Descriptions

Description	150W LED PRGRM DRVR 500-1500MA CC
extra long description	FUL T1M1UNV150P150L 150W, 0-10V, Ou
Long Description	WorkHorse LED Extreme - Single Channel - 0-10V Dimming LED Driver - Universal Voltage Input - Programmable 500-1500mA Constant Current Output - 150W Max - Linear Case w/ End Terminals - IP65
Product Type	150W, 0-10V, Outdoor PRG
Special Features	Programmable, 0-10 V Dimming

Manufacturer Information

Brand	Fulham
GTIN	10847098038242
Manufacturers Part Number	T1M1UNV150P150L
UPC	847098038245

Taxonomies, Classifications, and Categories

Category Description	DIMMING BALLASTS
Type	ELECTRONIC



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	20
Weight Per each	2.251

Uses, Certifications, and Standards

Application	Commercial & Residential
Frequency Rating	50/60
Mounting	Universal Mounting
standard	cULus Classified