



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

T70BWH8 Raceway Base

Panduit Corporation

Catalog Number	T70BWH8
Manufacturer	Panduit Corporation
Description	The T-70 Raceway Base Provides Solutions For Routing Low Voltage, Fiber Optic, and/or Power Cabling Along Perimeter Walls. The T-70 Raceway Is Supplied With Pre-Punched Mounting Holes and Is Tamper Resistant. It Is 8 FT and White.
Weight per unit	1.0 (lbs/each)
Product Category	Ducts, Raceways, Runways, Tray

Features

Cover Type	Multi-Channel
Material	Polyvinyl Chloride (PVC)
media	Yes

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Height	1.77
Length	8
Width	4.07

Descriptions

Description	RACEWAY BASE
extra long description	PAN T70BWH8 Surface Raceway, T-70 B
Long Description	The T-70 raceway base provides solutions for routing low voltage, fiber optic, and/or power cabling along perimeter walls. The T-70 raceway is supplied with pre-punched mounting holes and is tamper resistant. It is 8 ft and White.
Product Type	Surface Raceway, T-70 Base, 8 FT, White

Manufacturer Information

Brand	PANDUIT
GTIN	00074983725984
Manufacturers Part Number	T70BWH8
UPC	074983725984

Taxonomies, Classifications, and Categories

Category Description	Panduit & Wiremold Metallic & Non-Metallic Raceways
Type	Surface Raceway Channel

Availability

minimum qty	8
-------------	---



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	8
Package	48
Weight Per foot	1

Uses, Certifications, and Standards

Application	Provides Solutions for Routing Low Voltage, Fiber Optic and/or Power Cabling Along Perimeter Walls.T-70 Features the Workstation Outlet Center™ Offset Box, Which Provides an Offset Solution to Maximize Channel Capacity and Outlet Density.
standard	CE Compliant, UL5A Listed, UL Listed 95425, UL Listed E116129