



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TB25 3/4" Alu TB SR5 Conduit Body

Crouse-Hinds

Catalog Number	TB25
Manufacturer	Crouse-Hinds
Description	Conduit Outlet Body, Epoxy Powder Painted (Body); Natural (Gasket), 3/4 In Trade Size, 7.5 Cu.In Capacity, 90 ° Angle, 3/4 In Hub Size, 5.51 In Length, 2.4 In Width, 1.53 In Height, 0.34 LB/Ea
Weight per unit	0.3400 (lbs/each)
Product Category	Alum

Features

connection	Threaded / Set Screw
dimensions	5.5100 IN X 1.5300 IN X 2.4000 IN
Form	Series 5

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Length	5.51
Width	2.40

Descriptions

Description	3/4" ALU TB SR5 CONDUIT BODY
extra long description	CRS-H TB25 3/4 RGD TB COND BODY AL
Features	Eaton's Crouse-Hinds Division Series 5 die cast copper-free aluminum conduit bodies, covers and gaskets are available for use with rigid or EMT conduit (with set screw). Conduit bodies are available in trade sizes 1/2" to 4", in the most popular conduit body shapes (C, LB, LL, LR, T) and 1/2" to 2" in TB and X shapes. The Series 5 family is available as components or pre-packaged in various configurations as a SnapPack assembly. In addition, Series 5 is completely interchangeable with other manufacturer

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00662277008518
UPC	662277008518

Taxonomies, Classifications, and Categories

Category Description	HUB STYLE BOXES (GUAB, GUAT, ETC)
Type	Conduit outlet body



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.34

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure	Condulet
Mounting standard	Conduit UL, cUL