

Eaton TB67 CG

Catalog Number: TB67 CG

Eaton Crouse-Hinds series Condulet Form 7 SnapPack conduit outlet body, gasket and cover, Feraloy iron alloy, TB shape, 2"

General specifications



Photo is representative

| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series Condulet Form 7 SnapPack conduit outlet body, gasket and cover | TB67 CG |
| | UPC |
| | 782274141442 |
| Product Length/Depth | Product Height |
| 9.19 in | 6.13 in |
| Product Width | Product Weight |
| 3 in | 5.84 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

12

Product specifications

Shape

TB

Trade size

2"

Material

Feraloy iron alloy

Resources

Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

Installation instructions

[IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

Specifications and datasheets

[Eaton Specification Sheet - TB67 CG](#)

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton TB67 CG

Catalog Number: TB67 CG

Eaton Crouse-Hinds series Condulet Form 7 SnapPack conduit outlet body, gasket and cover, Feraloy iron alloy, TB shape, 2"

General specifications



Photo is representative

| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series Condulet Form 7 SnapPack conduit outlet body, gasket and cover | TB67 CG |
| | UPC |
| | 782274141442 |
| Product Length/Depth | Product Height |
| 9.19 in | 6.13 in |
| Product Width | Product Weight |
| 3 in | 5.84 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

12

Product specifications

Shape

TB

Trade size

2"

Material

Feraloy iron alloy

Resources

Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

Installation instructions

[IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

Specifications and datasheets

[Eaton Specification Sheet - TB67 CG](#)

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)