

Eaton TCF40

Catalog Number: TCF40

Eaton Bussmann series TCF fuse, 40 A, 60 Hz, 50 Hz, Dual, CF, Black, Blade end, Time delay, Class CF, 10 sec at 500%, 100 kAIC at 300 Vdc, 300 kAIC at 600 V, Glass filled PES, 35 mm DIN rail, Chassis, 600 V, 300 Vdc

General specifications

Product Name	Catalog Number
Eaton Bussmann series TCF fuse	TCF40
UPC	EAN
051712615051	5027590116992
Product Length/Depth	Product Height
2.13 in	1.9 in
Product Width	Product Weight
1 in	0.17 lb
Warranty	Compliances
Not Applicable	CE Marked RoHS Compliant
Certifications	
UL Listed CSA Certified	



Electrical rating

Amperage Rating

40 A

Frequency rating - max

60 Hz

Frequency rating - min

50 Hz

Interrupt rating

100 kAIC at 300 Vdc

300 kAIC at 600 Vac

Response time

10 sec at 500%

Voltage rating

600 Vac, 300 Vdc

Physical details

Color

Black

Fuse type

Class CF

Time delay

Material

Glass filled PES

Number of elements

Dual

Packaging type

Standard

General information

Class

Class CF

Connection

Blade end

Fuse indicator

With Indicator

Mounting method

Chassis

35 mm DIN rail

Special features

Finger safe

Used with

TCFH60N, CCP2-3-60CF

Resources

Catalogs

[Bussmann Full Line Catalog](#)

[Low Voltage Branch Circuit Fuse Chapter](#)

Compliance information

[RoHS Search Tool](#)

Multimedia

The Power of Space

Bussmann series Fuseology

Technical data sheets

Bussmann series UL Class CF CUBEFuse data sheet no. 9000



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton TCF40

Catalog Number: TCF40

Eaton Bussmann series TCF fuse, 40 A, 60 Hz, 50 Hz, Dual, CF, Black, Blade end, Time delay, Class CF, 10 sec at 500%, 100 kAIC at 300 Vdc, 300 kAIC at 600 V, Glass filled PES, 35 mm DIN rail, Chassis, 600 V, 300 Vdc

General specifications

Product Name	Catalog Number
Eaton Bussmann series TCF fuse	TCF40
UPC	EAN
051712615051	5027590116992
Product Length/Depth	Product Height
2.13 in	1.9 in
Product Width	Product Weight
1 in	0.17 lb
Warranty	Compliances
Not Applicable	CE Marked RoHS Compliant
Certifications	
UL Listed CSA Certified	



Electrical rating

Amperage Rating

40 A

Frequency rating - max

60 Hz

Frequency rating - min

50 Hz

Interrupt rating

100 kAIC at 300 Vdc

300 kAIC at 600 Vac

Response time

10 sec at 500%

Voltage rating

600 Vac, 300 Vdc

Physical details

Color

Black

Fuse type

Class CF

Time delay

Material

Glass filled PES

Number of elements

Dual

Packaging type

Standard

General information

Class

Class CF

Connection

Blade end

Fuse indicator

With Indicator

Mounting method

Chassis

35 mm DIN rail

Special features

Finger safe

Used with

TCFH60N, CCP2-3-60CF

Resources

Catalogs

[Bussmann Full Line Catalog](#)

[Low Voltage Branch Circuit Fuse Chapter](#)

Compliance information

[RoHS Search Tool](#)

Multimedia

The Power of Space

Bussmann series Fuseology

Technical data sheets

Bussmann series UL Class CF CUBEFuse data sheet no. 9000



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)