

Eaton TCF60RN

Catalog Number: TCF60RN

Eaton Bussmann Series Class CF fuse, TCF, time-delay, dual-element current limiting cube fuse, 60 A, non-indicating fuse, interrupting rating of 100 kA at 300 Vdc and 300 kA at 600 Vac

General specifications



Product Name	Catalog Number
Eaton Bussmann series TCF fuse	TCF60RN
UPC	Product Length/Depth
051712222556	2.13 in
Product Height	Product Width
1.9 in	1 in
Product Weight	Warranty
0.17 lb	Not Applicable
Compliances	Certifications
CE Marked	UL Listed
RoHS Compliant	CSA Certified

Electrical rating

Amperage Rating

60 A

Frequency rating - max

60 Hz

Frequency rating - min

50 Hz

Interrupt rating

100 kAIC at 300 Vdc

300 kAIC at 600 Vac

Response time

10 sec at 500%

Voltage rating

600 Vac, 300 Vdc

Physical details

Color

Black

Fuse type

Class CF

Time delay

Material

Glass filled PES

Number of elements

Dual

Packaging type

Standard

General information

Class

Class CF

Connection

Blade end

Fuse indicator

Non-indicating

Mounting method

Chassis

35 mm DIN rail

Special features

Finger safe

Used with

TCFH60N, CCP2-3-60CF

Resources

Catalogs

[Bussmann Full Line Catalog](#)

[Low Voltage Branch Circuit Fuse Chapter](#)

Compliance information

[RoHS Search Tool](#)

Multimedia

The Power of Space

Bussmann series Fuseology

Technical data sheets

Bussmann series UL Class CF CUBEFuse data sheet no. 9000



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)