

# Eaton TCF70

Catalog Number: TCF70

Eaton Bussmann series TCF fuse, 70 A, 60 Hz, 50 Hz, Dual, CF, Black, With indicator, Blade end, Time delay, 10 sec at 500%, 100 kAIC at 300 Vdc, 300 kAIC at 600 V, Glass filled PES, Chassis, 35 mm DIN rail, 600 V, 300 Vdc



## General specifications

Product Name	Catalog Number
Eaton Bussmann series TCF fuse	TCF70
UPC	EAN
051712618151	5027590247573
Product Length/Depth	Product Height
3.01 in	2.125 in
Product Width	Product Weight
1 in	0.284 lb
Warranty	Compliances
Not Applicable	CE Marked
	RoHS Compliant
Certifications	
UL Listed	
CSA Certified	

## Electrical rating

### Amperage Rating

70 A

### Frequency rating - max

60 Hz

### Frequency rating - min

50 Hz

### Interrupt rating

300 kAIC at 600 Vac

100 kAIC at 300 Vdc

### Response time

10 sec at 500%

### Voltage rating

600 Vac, 300 Vdc

## Physical details

### Color

Black

### Fuse type

Class CF

Time delay

### Material

Glass filled PES

### Number of elements

Dual

### Packaging type

Standard

## General information

### Class

Class CF

### Connection

Blade end

### Fuse indicator

With Indicator

### Mounting method

Chassis

35 mm DIN rail

### Special features

Finger safe

### Used with

TCFH30N, CCP2-3-30CF

## Resources

### Multimedia

[The Power of Space](#)

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - TCF70](#)

[Technical data sheets](#)

[TCF70~CUBEFUSE, TCF 70A IND](#)

[Technical service bulletins](#)

[Datasheet - FNQ-30](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)