



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4250 Business Center Dr. Suite 300
28214-0000, NC Charlotte
Phone: 980-249-1969
Fax: 704-900-0948

THHN4BKPCS THHN 4 STR Black PCS *Southwire Company*



Catalog Number	THHN4BKPCS
Manufacturer	Southwire Company
Description	THHN Building Wire, Heat, Moisture, Gasoline and Oil Resistant;Simpull(R) Technology For Easier Pulling Additional Information, Commercial;Industrial Application, Black, Copper Conductor Material, 4 Awg Conductor Size, 100 A (90°C);70 A (60°C);85 A (75°C) Current Rating, PVC Insulation Material, 40 Mil Insulation Thickness, Nylon Jacket Material, Made In Usa, +90 °C Maximum Operating Temperature, 19 - Strands, 318 Mil Outside Diameter, Reel;Spool Package Type, Csa C22.2 No. 75;Federal Specification A-A-595
Weight per unit	0.1520 (lbs/ft)
Product Category	THHN-T90-STR (Stranded)

Features

Tip Size	By-the-foot
----------	-------------

Descriptions

Description	THHN 4 STR BLACK PCS
-------------	----------------------

Manufacturer Information

Brand	Copper
-------	--------

Taxonomies, Classifications, and Categories

Category Description	BUILDING WIRE
----------------------	---------------

Packaging

Carton	1
Weight Per foot	0.152