ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
320 SW 28TH ST
72712-0000, AR Bentonville
Phone: 479-250-1930
Fax: 479-250-1931



THQL2130 2P 30A 120/240V Plug-In Circuit Breaker

Industrial Connections &

Catalog Number	THQL2130
Manufacturer	Industrial Connections &
Description	THQL 2 Pole 120/240V 10K Ic 30 Amp
Weight per unit	650.0 (lbs/each)
Product Category	2 Pole Standard Trip Plug-In

Features

amperage rating	30
frame	Q-Line
interrupt rating	10kA@120 Vac / 10kA@120/240 Vac
Load Rating	HACR
Poles	2
trip range	Non-Interchangeable
Trip Type	LI
Voltage Rating	240 V

Descriptions

Description	2P 30A 120/240V PLUG-IN CIRCUIT BREAKER
extra long description	GE THQL2130 THQL 2 POLE 120/240V 10
Long Description	THQL 2 POLE 120/240V 10K IC 30 AMP
Product Type	THQL 2 Pole 120/240V 10K Ic 30 Amp
Special Features	Q Line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications in load centers or lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. The THQL2130 breaker features 2 poles, an ampere

Manufacturer Information

Brand	GE
GTIN	00783164012927
Manufacturers Part Number	THQL2130
UPC	783164012927

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
320 SW 28TH ST
72712-0000, AR Bentonville
Phone: 479-250-1930
Fax: 479-250-1931

Packaging

Carton	1
Weight Per each	650

Uses, Certifications, and Standards

Application	Thermal Magnetic
standard	E11592