



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1910 Business Interstate 35E
78061-0000, TX Pearsall
Phone: 830-334-5353
Fax: 830-334-5757



THQL2160 2P 60A 120/240 Plug-In Circuit Breaker

Industrial Connections &

Catalog Number	THQL2160
Manufacturer	Industrial Connections &
Description	THQL 2 Pole 120/240V 10K Ic 60 Amp
Weight per unit	680.0 (lbs/each)
Product Category	2 Pole Standard Trip Plug-In

Features

amperage rating	60
frame	Q-Line
interrupt rating	10kA@120 Vac / 10kA@120/240 Vac
Load Rating	HACR
Poles	2
trip range	Non-Interchangeable
Trip Type	LI
Voltage Rating	240 V

Descriptions

Description	2P 60A 120/240 PLUG-IN CIRCUIT BREAKER
extra long description	GE THQL2160 THQL 2 POLE 120/240V 10
Long Description	THQL 2 POLE 120/240V 10K IC 60 AMP
Product Type	THQL 2 Pole 120/240V 10K Ic 60 Amp
Special Features	Q Line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications in load centers or lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. The THQL2160 breaker features 2 poles, an amper

Manufacturer Information

Brand	GE
GTIN	00783164048483
Manufacturers Part Number	THQL2160
UPC	783164048483

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
----------------------	----------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1910 Business Interstate 35E
78061-0000, TX Pearsall
Phone: 830-334-5353
Fax: 830-334-5757

Packaging

Carton	1
Weight Per each	680

Uses, Certifications, and Standards

Application	Thermal Magnetic
standard	E11592