

---

## TAMPER-RESISTANT FLOOR BOX THERMOPLASTIC COVER, GRAY

TM1542TRGRY | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Thermoplastic Cover Includes 15 amp 125 volt Decorator receptacle, matching detachable and replaceable hinged door; threaded device-mounting holes; drill guides for low-voltage poke-through holes; accepts any Decorator device; mounts on carpeting, hardwood, linoleum, tile floors; Four mounting/leveling screws. Gray.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

- Tamper-Resistant shutters let plugs in, keep other things out.
- Hinged door is removable and easily replaceable.
- Durable construction, impact, and scratch resistant PVC construction.
- Standard Decorator opening that accepts GFCI, TVSS, DataCom, or other Decorator devices.
- Auto/Clamps and knockouts on both sides of box.
- Meets UL514(c) scrub water exclusion test.
- Threaded device mounting holes.
- Simple mounting box, fits into a 4 3/4 inch hole and mounts with 3 screws included.
- Ready for low-voltage wiring, drill guides on underside of cover.
- UL and cUL Listed. Captive screws on TM1542 Series -- screws will not be lost -- new.
- Made in USA.

---

### SPECIFICATIONS

#### GENERAL INFO

Product Series: Slater  
Component Type: Covers & Flanges

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: No  
UN SPSC: 39121308  
UR: No

## DIMENSIONS

Diameter (US): 6.5"

## TECHNICAL INFORMATION

Material: Plastic

Floor Type: Wood

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

