



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TM873NICC10 Decor Switch 3W 15A 120/277VAC Nickel

*Pass & Seymour/Legrand*

|                  |  |
|------------------|--|
| Catalog Number   | TM873NICC10  |
| Manufacturer     | Pass & Seymour/Legrand   |
| Description      | Allowing Control Of A Light or Fixture From Two Separately Located Switches, The Radiant® 3-Way Switch Upgrades Your Space With Clean Lines and Smooth Paddle Action For A Sophisticated Touch. Made Exclusively For Use With Screwless Wall Plates From The Radiant® Collection, Sold Separately. |
| Weight per unit  | 0.1775 (lbs/each)  |
| Product Category | Gen Purpose Switches   |

### Features

|                    |                     |
|--------------------|---------------------|
| actuator           | Rocker switch       |
| amperage rating    | 15                  |
| Contact Rating     | 15 Amp, 120/125 VAC |
| Material           | Thermoplastic       |
| media              | Yes                 |
| Mounting Type      | Box                 |
| Number of Gangs    | 1.0                 |
| Number of Switches | 1.0                 |
| operating cycles   | 50000               |
| Poles              | 3-Way, 1            |
| Switch Type        | Paddle              |
| Voltage            | 120/277 V           |
| Voltage Rating     | 120                 |
| Wire Size          | #14 - #10 Awg       |

### Material, Color, and Finish

|        |          |
|--------|----------|
| Color  | Nickel   |
| Finish | Metallic |

### Dimensions and Weight

|      |  |
|------|--|
| Size | 1.27" Depth x 1.43" Width x 4.19" Height |
|------|--|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | DECOR SWITCH 3W 15A 120/277VAC NICKEL   |
| extra long description | P&S TM873NICC10 3-WAY DECOR SW 15A  |
| Long Description       | Allowing control of a light or fixture from two separately located switches, the radiant® 3-Way Switch upgrades your space with clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.                        |
| Product Type           | 3-Way Decor SW 15A 120/277VAC Nickel  |
| Special Features       | Everyone wants a home that's a step above ordinary. Now the radiant® collection of switches, outlets, dimmers and home automation controls by Legrand puts that stylish finishing touch affordably within reach. radiant gets rid of unsightly screws, delivering clean looks in a range of colors and metallic finishes. |

## Manufacturer Information

|                           |                        |
|---------------------------|------------------------|
| Brand                     | LEGRAND-PASS & SEYMOUR |
| GTIN                      | 00785007021028         |
| Manufacturers Part Number | TM873-NICC10           |
| UPC                       | 785007021028           |

## Taxonomies, Classifications, and Categories

|                      |                    |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type                 | SWITCH             |

## Trade Size

|          |      |
|----------|------|
| Amperage | 15.0 |
|----------|------|

## Packaging

|                 |        |
|-----------------|--------|
| Carton          | 10     |
| Weight Per each | 0.1775 |

## Uses, Certifications, and Standards

|                          |  |
|--------------------------|--|
| Application              | Residential                              |
| environmental conditions | UL94 V2                                  |
| Mounting                 | BOX                                      |
| Operating Temperature    | Maximum continuous +115°C, minimum -40°C |
| standard                 | CULUS, CSA Listed, UL Listed             |