



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TM874BK Radiant Switch 4W 15A 120/277V BK *Pass & Seymour/Legrand*

| | |
|------------------|--|
| Catalog Number | TM874BK |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Nafta-Compliant Decorator Switch, 4WAY 15AMP 120/277V, Black |
| Weight per unit | 0.2694 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-------------|---------------|
| gang | 1 |
| insulation | Bare |
| Material | Thermoplastic |
| media | Yes |
| orientation | Vertical |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|-----------|-------|
| Size | 6.25" |
| Thickness | 2" |

Descriptions

| | |
|------------------------|---|
| Description | RADIANT SWITCH 4W 15A 120/277V BK |
| extra long description | P&S TM874BK RADIANT SWITCH 4W 15A 1 |
| Long Description | NAFTA-Compliant Decorator Switch,4Way 15Amp 120/277V, Black |
| Product Type | Radiant Switch 4W 15A 120/277V BK |
| Special Features | Designer style satin finish rocker, push wire 14awg, narrow back body |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007845037 |
| Manufacturers Part Number | TM874BK |
| UPC | 785007845037 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type | SWITCH |

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 100 |
| Weight Per each | 0.2694 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| standard | UL 20 |