



15A 4-WAY SWITCH, GRAY

TM874GRY | [radiant](#)

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

radiant® Screwless Wall Plate not included.

- Part of the all-new radiant® collection.
- Smooth paddle action.
- High-impact resistant thermoplastic construction.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Push wire #14 AWG.
- Narrow back body leaves more room for wires in the box.
- Extra-long, through-body strap eliminates floating installations and imperfect applications.
- Easy-access green hex head ground screw.
- Tri-drive ground, terminal and mounting screws.
- ON/OFF switches conform to NEC® 430-104 requirements for kitchen and disposal units
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Gray

Number Of Poles: 4-way

Special Features: Grounding

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 111

CSA Standard: Yes

UL Listing No: UL20

UL Standard: Yes

UN SPSC: 39121704

CONSTRUCTION INFORMATION

Component 4: 78500706050

DIMENSIONS

Depth (US): 1.27'

Height (US): 4.19"

Width (US): 1.43"

TECHNICAL INFORMATION

Amps: 15A

Volts: 120/277VAC

Volts (AC): 120/277

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Buy American Act Compliant





15A 4-WAY SWITCH, GRAY

TM874GRY | [radiant](#)

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

radiant® Screwless Wall Plate not included.

- Part of the all-new radiant® collection.
- Smooth paddle action.
- High-impact resistant thermoplastic construction.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Push wire #14 AWG.
- Narrow back body leaves more room for wires in the box.
- Extra-long, through-body strap eliminates floating installations and imperfect applications.
- Easy-access green hex head ground screw.
- Tri-drive ground, terminal and mounting screws.
- ON/OFF switches conform to NEC® 430-104 requirements for kitchen and disposal units
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Gray

Number Of Poles: 4-way

Special Features: Grounding

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 111

CSA Standard: Yes

UL Listing No: UL20

UL Standard: Yes

UN SPSC: 39121704

CONSTRUCTION INFORMATION

Component 4: 78500706050

DIMENSIONS

Depth (US): 1.27'

Height (US): 4.19"

Width (US): 1.43"

TECHNICAL INFORMATION

Amps: 15A

Volts: 120/277VAC

Volts (AC): 120/277

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Buy American Act Compliant

