



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TM874GRY Decor Switch 3W 15A 120/277V W/GRD Gy *Pass & Seymour/Legrand*

Catalog Number	TM874GRY
Manufacturer	Pass & Seymour/Legrand
Description	15A 120V 4-Way Decorator Switch, Gray
Weight per unit	0.2700 (lbs/each)
Product Category	Gen Purpose Switches

Features

actuator	Rocker switch
amperage rating	15
Contact Rating	120V
Material	Thermoplastic
media	Yes
Mounting Type	Box
Number of Gangs	1.0
Number of Switches	1.0
operating cycles	50000
Poles	4-Way, Single Pole
Switch Type	Paddle
Voltage	120/277 V
Voltage Rating	120

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	1.27" Depth x 1.43" Width x 4.19" Height
------	--

Descriptions

Description	DECOR SWITCH 3W 15A 120/277V W/GRD GY
extra long description	P&S TM874GRY DECOR SWITCH 3W 15A 12
Long Description	15A 120V 4-Way Decorator Switch, Gray
Product Type	Decor Switch 3W 15A 120/277V W/GRD Gy
Special Features	Everyone wants a home that's a step above ordinary. Now the radiant® collection of switches, outlets, dimmers and home automation controls by Legrand puts that stylish finishing touch affordably within reach. radiant gets rid of unsightly screws, delivering clean looks in a range of colors and metallic finishes.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007060508
Manufacturers Part Number	TM874GRY
UPC	785007060508

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
Type	Decorator Switch

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	10
Package	100
Weight Per each	0.27

Uses, Certifications, and Standards

Application	Residential
environmental conditions	UL94 V2
Mounting	BOX
Operating Temperature	Maximun continuous +115°C, minimum -40°C
standard	CULUS, CSA Listed, UL Listed