



## USB CHARGER WITH TAMPER-RESISTANT RECEPTACLE, LIGHT ALMOND

TM8USBLACC6 | [Pass & Seymour](#)

### FEATURES & BENEFITS

Charge more devices with less clutter. Legrand's full line of charging solutions is designed to power up mobile devices quickly and reliably—without the need for bulky AC adapters.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



- Charge two devices simultaneously while still using the receptacle.
- Compatible with USB 2.0 & 3.0 compatible devices.
- Total charging capacity of 2.1A.
- AC receptacles are tamper-resistant to meet NEC® Code—patented shutter system prevents improper insertion of foreign objects.
- Back and side wire terminals accommodate #14AWG - #10 AWG stranded and solid copper wire for installation flexibility.
- Accepts standard Pass & Seymour Wall Plates.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Light Almond

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

ETL Listing No: 4001804

ETL Listed: Yes

#### DIMENSIONS

Depth (US): 1.6"

Height (US): 2.7"

Width (US): 1.7"

**TECHNICAL INFORMATION**

Amps: 15A

Volts: 125V

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA

Buy American Act Status: No



## USB CHARGER WITH TAMPER-RESISTANT RECEPTACLE, LIGHT ALMOND

TM8USBLACC6 | [Pass & Seymour](#)

### FEATURES & BENEFITS

Charge more devices with less clutter. Legrand's full line of charging solutions is designed to power up mobile devices quickly and reliably—without the need for bulky AC adapters.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



- Charge two devices simultaneously while still using the receptacle.
- Compatible with USB 2.0 & 3.0 compatible devices.
- Total charging capacity of 2.1A.
- AC receptacles are tamper-resistant to meet NEC® Code—patented shutter system prevents improper insertion of foreign objects.
- Back and side wire terminals accommodate #14AWG - #10 AWG stranded and solid copper wire for installation flexibility.
- Accepts standard Pass & Seymour Wall Plates.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Light Almond

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

ETL Listing No: 4001804

ETL Listed: Yes

#### DIMENSIONS

Depth (US): 1.6"

Height (US): 2.7"

Width (US): 1.7"

**TECHNICAL INFORMATION**

Amps: 15A

Volts: 125V

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA

Buy American Act Status: No