

Eaton CGFP194

Catalog Number: CGFP194

Eaton Crouse-Hinds series CGFP cable gland, Non-armoured and tray cable, Non-armoured gland, Steel, Outer sheath min/max: 0.375-0.500", General purpose, 1/2" NPT

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series CGFP cable gland	CGFP194
	UPC
	782274152103
Product Length/Depth	Product Height
2.13 in	1.28 in
Product Width	Product Weight
1.28 in	0.2 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Protection type

General purpose

Cable type

Non-armoured

Tray cable

Gland type

Non-armoured

Thread Size

1/2"

Thread type

NPT

Outer sheath (min/max)

0.375-0.500"

Material

Steel

Resources

Brochures

[Crouse-Hinds series Tray Cable Glands brochure](#)

Catalogs

[Crouse-Hinds series CGB, CGD, CGE and CGFP Non-armoured Glands catalog page](#)

Certification reports

[CGB, CGD, CGE and CGFP Non-armoured Glands UL certification \(Cover\)](#)

[CGB, CGD, CGE and CGFP Non-armoured Glands UL certification](#)

Installation instructions

[IF 513A - CG Fittings Installation](#)

[IF 66 - CGFP Cable Terminator](#)

Specifications and datasheets

[Eaton Specification Sheet - CGFP194](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)