

Eaton TMCX050 1 L

Catalog Number: TMCX050 1 L

Eaton Crouse-Hinds series Terminator II TMCX cable gland, Liquid compound, Cable Range: 0.49-0.90", Cable Sealing: 1 (S), Metal-clad corrugated armoured, TECK armoured, armoured barrier and tray cable, Armoured gland, Aluminum, 1/2" NPT

General specifications

| | |
|--|----------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series Terminator II TMCX cable gland | TMCX050 1 L |
| | UPC |
| | 662276303386 |
| Product Length/Depth | Product Height |
| 4.05 in | 1.75 in |
| Product Width | Product Weight |
| 1.75 in | 0.78 lb |

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class II, Division 1

Class III

NEMA Rating

6P

4X

Product specifications

Protection type

Explosion-proof

Cable type

TECK armoured

Metal-clad with interlocked or continuously welded corrugated armoured

Tray cable

Armoured barrier

Gland type

Armoured

Thread Size

1/2"

Thread type

NPT

Cable sealing range

1 (S)

Cable range (min/max)

0.49-0.90"

Material

Aluminum

Barrier type

Liquid Compound

Resources

Brochures

[Crouse-Hinds series TMCX II brochure](#)

[Crouse-Hinds series Chico LiquidSeal flyer](#)

Catalogs

[Crouse-Hinds series TMCX II catalog page](#)

Certification reports

[TMCX II Explosionproof Armoured Barrier and Non-armoured Barrier](#)

[Gland UL certification](#)

[TMCX II Explosionproof Armoured Barrier and Non-armoured Barrier](#)

[Gland Canadian certification](#)

Installation instructions

IF 1647B - TMCX Terminator II Cable Gland

IF 1647 - TMCX Terminator II Cable Gland

Specifications and datasheets

Eaton Specification Sheet - TMCX050 1 L



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)