

# Eaton TMCX165

Catalog Number: TMCX165

Eaton Crouse-Hinds series TMCX cable gland, Metal-clad corrugated, TECK armoured and tray cable, Armoured barrier and non-armoured barrier, Aluminum, Outer Sheath: 0.49-0.78", 1/2" NPT, Armor Range: 0.44-0.65"



## General specifications

|  |                |
|--|----------------|
| Product Name                               | Catalog Number |
| Eaton Crouse-Hinds series TMCX cable gland | TMCX165        |
|  | UPC            |
|  | 782274414669   |
| Product Length/Depth                       | Product Height |
| 3.38 in                                    | 1.38 in        |
| Product Width                              | Product Weight |
| 1.38 in                                    | 0.08 lb        |

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class II, Division 1

Class III

### NEMA Rating

4

## Product specifications

### Protection type

Explosion-proof

### Cable type

Metal-clad with interlocked or continuously welded corrugated armoured

TECK armoured

Tray cable

### Gland type

Armoured Barrier and Non-armoured Barrier

### Material

Aluminum

### Thread Size

1/2"

### Thread type

NPT

### Armor (min/max)

0.44-0.65"

### Outer sheath (min/max)

0.49-0.78"

## Resources

### Catalogs

[Crouse-Hinds series TMCX catalog page](#)

### Certification reports

[TMCX Explosionproof Armoured Barrier Gland UL certification](#)

### Installation instructions

[IF 1184 - TMCX Terminator Cable Fittings](#)

### Specifications and datasheets

[Eaton Specification Sheet - TMCX165](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)