



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## TMRP Series Timing Relay

TMRP5100

UPC:786685215358

### Dimensions:

- **Height:** 1.88 IN
- **Length:** 3.46 IN
- **Width:** 1.88 IN

**Weight:**3 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Contact Configuration:** DPDT
- **Contact Material:** 90% silver, 10% nickel
- **Contact Rating:** 12A
- **Number Of Pins:** 11
- **Functions:** Power triggered, flasher-pause or ON first, single shot leading edge voltage controlled and control input, retriggerable single shot, single pulse generator, ON/OFF delay, memory latch
- **Input Voltage:** 12-240 Vac/dc
- **Operating Mode:** Control switch trigger
- **Options:** Plastic dust cover
- **Series:** TMRP series
- **Terminals:** Octal
- **Time Delay:** 0.1 seconds-9990 hours

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - TMRP5100](#)

### Certifications:



- UL Listed

**Product compliance:**

- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## TMRP Series Timing Relay

TMRP5100

UPC:786685215358

### Dimensions:

- **Height:** 1.88 IN
- **Length:** 3.46 IN
- **Width:** 1.88 IN

**Weight:**3 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Contact Configuration:** DPDT
- **Contact Material:** 90% silver, 10% nickel
- **Contact Rating:** 12A
- **Number Of Pins:** 11
- **Functions:** Power triggered, flasher-pause or ON first, single shot leading edge voltage controlled and control input, retriggerable single shot, single pulse generator, ON/OFF delay, memory latch
- **Input Voltage:** 12-240 Vac/dc
- **Operating Mode:** Control switch trigger
- **Options:** Plastic dust cover
- **Series:** TMRP series
- **Terminals:** Octal
- **Time Delay:** 0.1 seconds-9990 hours

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - TMRP5100](#)

### Certifications:



- UL Listed

**Product compliance:**

- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.