



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TMTR750J Terminator Tan/Red 750PC Jar *Nsi Industries*

Catalog Number	TMTR750J
Manufacturer	Nsi Industries
Description	Terminator Tan/Red Premium Wire Connectors With Steel Springs, Rated For Copper Wire In 18-12 Awg Wire Range. Dual Color Coding Means One Premium Wire Connector Does The Job Of Two Standard Connectors In Most Applications.
Weight per unit	2.4 (lbs/each)
Product Category	Tools & Testers

Features

Material	Thermoplastic
Voltage Rating	600
Warranty	1 YEAR
Wire Type	CU Wire Only

Material, Color, and Finish

Color	Red/Tan
Finish	Thermoplastic

Dimensions and Weight

Size	H=1.205 - W=.730
------	------------------

Descriptions

Description	TERMINATOR TAN/RED 750PC JAR
extra long description	NSI TM-TR-750J Terminator T/R Jar 7
Features	Terminator Tan/Red 750pc Jar
Long Description	TERMINATOR Tan/Red Premium Wire Connectors with Steel Springs, Rated for copper wire in 18-12 AWG Wire Range. Dual color coding means one premium wire connector does the job of two standard connectors in most applications.
Product Type	Terminator T/R Jar 750PC
Special Features	Flexible Skirt covers over strip and conforms to fit into tight spaces - Fixed precise square wire spring provides secure gripping of conductors - Flame retardant UL 94V-2 thermoplastic shell provides excellent electrical insulation - Zinc-plated spring for low contact resistance

Manufacturer Information

Brand	NSi
GTIN	00662381365361
Manufacturers Part Number	TM-TR-750J
UPC	662381365361



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Tan/Red

Packaging

Carton	1
Weight Per jar	2.42

Uses, Certifications, and Standards

Application	Splicing Wire
environmental conditions	105
standard	UL 486C
Temperature Rating	105