

Eaton TN225ZN

Catalog Number: TN225ZN

Eaton B-Line series Twirl-Nut nut, 0.25"Hx1.375"Lx0.85"W, Steel, Electro-plated, 1/2"-13 bolt size, 1500 lbs load, 1500 lbs load

General specifications



Product Name	Catalog Number
Eaton B-Line series Twirl-Nut nut	TN225ZN
UPC	Product Length/Depth
781011401535	1.375 in
Product Height	Product Width
0.25 in	0.85 in
Product Weight	Certifications
0.116 lb	Not Applicable

Model

Bolt/thread/rod size

1/2"-13

Product Category

Channel nuts

Type

Twirl-nut

Load rating/capacity

Load rating (pull out strength)

1500 lbs

Load rating (slip strength)

1500 lbs

Material/finish

Finish

Electro-plated

Material

Steel

Resources

Catalogs

[Channel Nuts and Hardware Catalog Section](#)

[B-Line Series Strut Systems Catalog](#)

[B-Line Safety Gratings Full Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - TN225ZN](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)