

Vinyl Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [TP1010](#)



Copper Terminal, Ring Tongue, 12-10 AWG, #8-#10 Stud, Vinyl Insulated, Tin Plated, Wire strip length: 19/64".

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

General

Color Code	Yellow
Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	Ring Tongue
UPC	781810710845
UPC 12 Digit	7818107108455

Dimensions

Cable Insulation Diameter Maximum	0.280 in
Dimension - B Length fraction	17/50 in
Dimension - B Length inch	0.34 in
Dimension - Bolt Size fraction	#10
Dimension - Diameter Max Size inch	0.28 in
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.03 mm
Dimension - Pad Width inch	0.35 in
Dimension - Strip Length inch	19/64 in
Dimension - Stud Size inch	#10
Dimension - Z inch	0.26 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600
Minimum Pack Quantity	50
Pallet Quantity	99999

Product Assets

[3D Models - TP1010_MODEL-IGES](#)
[3D Models - TP1010_MODEL-PDF](#)
[3D Models - TP1010_MODEL-STEP](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50093722](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-TP1010-SPEC-EN | REV 8/2023