



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TP14 Trademaster Wallplate 1G Blank Strap MT

Pass & Seymour/Legrand

| | |
|------------------|--------------------------------------------|
| Catalog Number | TP14 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Trademaster Plate 1-Gang Blank Strap Mount |
| Weight per unit | 0.0838 (lbs/each) |
| Product Category | Wall Plates & Covers |

Features

| | |
|-----------------|----------------|
| cutout | Blank |
| insulation | Bare |
| Mounting Type | Exposed Screws |
| Number of Gangs | 1 |
| orientation | Vertical |
| Wall Plate Type | Blank |

Dimensions and Weight

| | |
|-----------|------|
| Size | 5" |
| Thickness | 0.07 |

Descriptions

| | |
|------------------------|--------------------------------------------|
| Description | TRADEMASTER WALLPLATE 1G BLANK STRAP MT |
| extra long description | P&S TP14 TRADEMASTER PLT 1G BLANK S |
| Long Description | Trademaster Plate 1-Gang Blank Strap Mount |
| Product Type | Trademaster PLT 1G Blank Strap MT |
| Special Features | Standard size plastic smooth wall plate |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007274776 |
| Manufacturers Part Number | TP14 |
| UPC | 785007274776 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type | Wall Plate |

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 200 |
| Weight Per each | 0.0838 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| standard | CULUS, CSA, UL514 |