


Eaton TP158

Catalog Number: TP158

Eaton Crouse-Hinds series Switch Box, (1) 1/2", NM clamps, 2-1/2", Steel, Ears, Gangable, 12.5 cubic inch capacity



General specifications

| | |
|--------------------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series switch box | TP158 |
| UPC | Product Length/Depth |
| 786189101584 | 3 in |
| Product Height | Product Width |
| 2.5 in | 2 in |
| Product Weight | |
| 0.58 lb | |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Depth

2-1/2"

Type

Gangable

Capacity

12.5 cubic in

Conduit/cable

NM clamps

Bottom Knockouts

(1) 1/2 in

Material

Steel

Special features

Ears

Resources

Catalogs

[Crouse-Hinds series Steel Switch Boxes catalog page](#)

Certification reports

[Steel Switch Boxes Canadian certification](#)

[Steel Switch Boxes UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - TP158](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)