

# Eaton TP171

Catalog Number: TP171

Eaton Crouse-Hinds series Switch Box, (1) 1/2", VP, set 1/2", 2, NM clamps, 2-1/2", (1) 1/2", Steel, (1) 1/2", Gangable, 12.5 cubic inch capacity



## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series switch box	TP171
UPC	Product Length/Depth
786189101713	2 in
Product Height	Product Width
3 in	2.5 in
Product Weight	
0.73 lb	

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Depth

2-1/2"

### Type

Gangable

### Capacity

12.5 cubic in

### Conduit/cable

NM clamps

### Bracket style

VP, Set 1/2"

### End Knockouts

(1) 1/2 in

### Side knockouts

(1) 1/2 in

### Bottom Knockouts

(1) 1/2 in

### Cable knockouts

2

### Material

Steel

## Resources

### Catalogs

[Crouse-Hinds series Steel Switch Boxes catalog page](#)

### Certification reports

[Steel Switch Boxes Canadian certification](#)

[Steel Switch Boxes UL certification](#)

### Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP171](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton TP171

Catalog Number: TP171

Eaton Crouse-Hinds series Switch Box, (1) 1/2", VP, set 1/2", 2, NM clamps, 2-1/2", (1) 1/2", Steel, (1) 1/2", Gangable, 12.5 cubic inch capacity



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series switch box	TP171
<b>UPC</b>	<b>Product Length/Depth</b>
786189101713	2 in
<b>Product Height</b>	<b>Product Width</b>
3 in	2.5 in
<b>Product Weight</b>	
0.73 lb	

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Depth

2-1/2"

### Type

Gangable

### Capacity

12.5 cubic in

### Conduit/cable

NM clamps

### Bracket style

VP, Set 1/2"

### End Knockouts

(1) 1/2 in

### Side knockouts

(1) 1/2 in

### Bottom Knockouts

(1) 1/2 in

### Cable knockouts

2

### Material

Steel

## Resources

### Catalogs

[Crouse-Hinds series Steel Switch Boxes catalog page](#)

### Certification reports

[Steel Switch Boxes Canadian certification](#)

[Steel Switch Boxes UL certification](#)

### Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP171](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)