

# Eaton TP278

Catalog Number: TP278

Eaton Crouse-Hinds series Octagon Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), 1-1/2", Steel, (2) 1/2", (2) 3/4", Fixture rated, 15.5 cubic inch capacity

## General specifications



Photo is representative

|  |                       |
|--|-----------------------|
| <b>Product Name</b>                          | <b>Catalog Number</b> |
| Eaton Crouse-Hinds series octagon outlet box | TP278                 |
|  | UPC                   |
|  | 786189102789          |
| <b>Product Length/Depth</b>                  | <b>Product Height</b> |
| 4 in   | 1.5 in                |
| <b>Product Width</b>                         | <b>Product Weight</b> |
| 4 in   | 0.5 lb                |

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

4"

### Depth

1-1/2"

### Capacity

15.5 cubic in

### Conduit/cable

Conduit (no clamps)

### Side knockouts

(2) 1/2 in, (2) 3/4 in

### Bottom Knockouts

(3) 1/2 in, (2) 3/4 in

### Material

Steel

### Special features

Fixture rated

## Resources

### Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

### Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - TP278](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton TP278

Catalog Number: TP278

Eaton Crouse-Hinds series Octagon Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), 1-1/2", Steel, (2) 1/2", (2) 3/4", Fixture rated, 15.5 cubic inch capacity

## General specifications



Photo is representative

|  |                       |
|--|-----------------------|
| <b>Product Name</b>                          | <b>Catalog Number</b> |
| Eaton Crouse-Hinds series octagon outlet box | TP278                 |
|  | UPC                   |
|  | 786189102789          |
| <b>Product Length/Depth</b>                  | <b>Product Height</b> |
| 4 in   | 1.5 in                |
| <b>Product Width</b>                         | <b>Product Weight</b> |
| 4 in   | 0.5 lb                |

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

4"

### Depth

1-1/2"

### Capacity

15.5 cubic in

### Conduit/cable

Conduit (no clamps)

### Side knockouts

(2) 1/2 in, (2) 3/4 in

### Bottom Knockouts

(3) 1/2 in, (2) 3/4 in

### Material

Steel

### Special features

Fixture rated

## Resources

### Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

### Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - TP278](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)