

# Eaton TP282

Catalog Number: TP282

Eaton Crouse-Hinds series Octagon Outlet Box, (5) 1/2", 4", S, set 1/2", Conduit (no clamps), 1-1/2", Steel, (3) 1/2", Fixture rated, 15.5 cubic inch capacity



## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series octagon outlet box	TP282
	UPC
	786189102826
Product Length/Depth	Product Height
4 in	1.5 in
Product Width	Product Weight
4 in	0.58 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

4"

### Depth

1-1/2"

### Capacity

15.5 cubic in

### Conduit/cable

Conduit (no clamps)

### Bracket style

S, Set 1/2"

### Side knockouts

(3) 1/2 in

### Bottom Knockouts

(5) 1/2 in

### Material

Steel

### Special features

Fixture rated

## Resources

### Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

### Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

### Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP282](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton TP282

Catalog Number: TP282

Eaton Crouse-Hinds series Octagon Outlet Box, (5) 1/2", 4", S, set 1/2", Conduit (no clamps), 1-1/2", Steel, (3) 1/2", Fixture rated, 15.5 cubic inch capacity



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series octagon outlet box	TP282
	UPC
	786189102826
<b>Product Length/Depth</b>	<b>Product Height</b>
4 in	1.5 in
<b>Product Width</b>	<b>Product Weight</b>
4 in	0.58 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

4"

### Depth

1-1/2"

### Capacity

15.5 cubic in

### Conduit/cable

Conduit (no clamps)

### Bracket style

S, Set 1/2"

### Side knockouts

(3) 1/2 in

### Bottom Knockouts

(5) 1/2 in

### Material

Steel

### Special features

Fixture rated

## Resources

### Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

### Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

### Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP282](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)