

Specifications



Eaton TP632

Eaton Crouse-Hinds series Gang Box, (6) 1/2" and 3/4" concentric, VP, Conduit (no clamps), 2-1/2", (2) 1/2" and 3/4" concentric, Steel, Three-gang, (3) 1/2" and 3/4" concentric, Non-gangable, 46.5 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series gang box
CATALOG NUMBER	TP632
UPC	786189106329
PRODUCT LENGTH/DEPTH	5.56 in
PRODUCT HEIGHT	2.5 in
PRODUCT WIDTH	3.75 in
PRODUCT WEIGHT	1.43 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

DEPTH	2-1/2"
TYPE	Non-gangable
NUMBER OF GANGS	Three-gang
CAPACITY	46.5 cubic in

CONDUIT/CABLE	Conduit (no clamps)
BRACKET STYLE	VP
END KNOCKOUTS	(2) 1/2 in and 3/4 in concentric
SIDE KNOCKOUTS	(3) 1/2 in and 3/4 in concentric
BOTTOM KNOCKOUTS	(6) 1/2 in and 3/4 in concentric
MATERIAL	Steel

Resources

CATALOGS

[Crouse-Hinds series Steel Switch Boxes catalog page](#)

CERTIFICATION REPORTS

[Steel Switch Boxes UL certification](#)

[Steel Switch Boxes Canadian certification](#)

SPECIFICATIONS AND DATASHEETS

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP632](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

