

Specifications

Eaton TP672

Eaton Crouse-Hinds series Switch Box, (1) 1/2", Conduit (no clamps), 2-3/4", (1) 1/2", Steel, (1) 1/2", Gangable, 14.0 cubic inch capacity



General specifications

| | |
|-----------------------------|--------------------------------------|
| PRODUCT NAME | Eaton Crouse-Hinds series switch box |
| CATALOG NUMBER | TP672 |
| UPC | 786189106725 |
| PRODUCT LENGTH/DEPTH | 2 in |
| PRODUCT HEIGHT | 3 in |
| PRODUCT WIDTH | 2.75 in |
| PRODUCT WEIGHT | 0.59 lb |

Certifications and compliances

| | |
|----------------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE | NEC/CEC |

Product specifications

| | |
|-------------------------|---------------------|
| DEPTH | 2-3/4" |
| TYPE | Gangable |
| CAPACITY | 14 cubic in |
| CONDUIT/CABLE | Conduit (no clamps) |
| END KNOCKOUTS | (1) 1/2 in |
| SIDE KNOCKOUTS | (1) 1/2 in |
| BOTTOM KNOCKOUTS | (1) 1/2 in |
| MATERIAL | Steel |

Resources

| | |
|--------------------------------------|--|
| CATALOGS | Crouse-Hinds series Steel Switch Boxes catalog page |
| CERTIFICATION REPORTS | Steel Switch Boxes UL certification Steel Switch Boxes Canadian certification |
| SPECIFICATIONS AND DATASHEETS | Steel Outlet Boxes for Electrical Systems Eaton Specification Sheet - TP672 |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications

Eaton TP672

Eaton Crouse-Hinds series Switch Box, (1) 1/2", Conduit (no clamps), 2-3/4", (1) 1/2", Steel, (1) 1/2", Gangable, 14.0 cubic inch capacity



General specifications

| | |
|-----------------------------|--------------------------------------|
| PRODUCT NAME | Eaton Crouse-Hinds series switch box |
| CATALOG NUMBER | TP672 |
| UPC | 786189106725 |
| PRODUCT LENGTH/DEPTH | 2 in |
| PRODUCT HEIGHT | 3 in |
| PRODUCT WIDTH | 2.75 in |
| PRODUCT WEIGHT | 0.59 lb |

Certifications and compliances

| | |
|----------------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE | NEC/CEC |

Product specifications

| | |
|-------------------------|---------------------|
| DEPTH | 2-3/4" |
| TYPE | Gangable |
| CAPACITY | 14 cubic in |
| CONDUIT/CABLE | Conduit (no clamps) |
| END KNOCKOUTS | (1) 1/2 in |
| SIDE KNOCKOUTS | (1) 1/2 in |
| BOTTOM KNOCKOUTS | (1) 1/2 in |
| MATERIAL | Steel |

Resources

| | |
|--------------------------------------|--|
| CATALOGS | Crouse-Hinds series Steel Switch Boxes catalog page |
| CERTIFICATION REPORTS | Steel Switch Boxes UL certification Steel Switch Boxes Canadian certification |
| SPECIFICATIONS AND DATASHEETS | Steel Outlet Boxes for Electrical Systems Eaton Specification Sheet - TP672 |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

