

## Power Outlet Receptacle Openings, Two Gang, Ivory

TP703I



Two Gang Power Outlet Receptacle  
Opening, 2.1563" hole for 2.125" diameter  
device - 4 mtg. holes, Ivory Nylon.



### features & benefits

- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only.)
- Available in "TP" series, extra 3/16 inch width and height than Standard size plates; and "TPJ" series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070 inch.

### specifications

#### General Info

Color: Ivory

Size: Standard

Special Features: Unbreakable

#### Listing Agencies/Third Party Information

CSA Listing Info: No

CUL Listing No: No

cULus: Yes

cURus: No

Federal Spec: No

UL Listing No: No

UN SPS C: 39121704

UR: No

**Dimensions**

Diameter U S: 2.1563" Hole

**Technical Information**

Material: Nylon

Capacity: 2-gang

**Buy American Act Compliance**

Country of Origin: UNITED-STATES-OF-AMERICA

Buy American Act Status: Buy American Act Compliant