



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR20BK Duplex Recp TR 20A/125V BK

Pass & Seymour/LeGrand

| | |
|------------------|--|
| Catalog Number | TR20BK |
| Manufacturer | Pass & Seymour/LeGrand |
| Description | Tamper-Resistant Commercial Grade Receptacle, 20A, 125V. Available In 6 Colors. For Detailed Tamper-Resistant Receptacle Information, Visit Our Tamper-Resistant Receptacles Page. |
| Weight per unit | 0.2478 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|--|
| amperage rating | 20 |
| connection | Side wire |
| Dielectric Strength | Withstands 1500V minimum |
| indoor/outdoor | Indoor |
| Material | Nylon |
| media | Yes |
| Number of Wires | 3 |
| Outlet Type | Tamper-Resistant |
| Poles | 2 |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | 14 - 10 |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|--------|-------|
| Height | 3.281 |
| Width | 1.130 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | DUPLEX RECP TR 20A/125V BK |
| extra long description | P&S TR20BK RECEP DUP TAMPER RESIS 2 |
| Long Description | Tamper-Resistant Commercial Grade Receptacle, 20A, 125V. Available in 6 colors. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page. |
| Product Type | Recep Dup Tamper Resis 20A/125V BK |
| Special Features | Dual mechanical shutter system to help prevent insertion of foreign objects. Auto-ground clip assures positive ground. Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring. Backed-out tri-drive steel terminal screws for faster installation. Side wire capability. Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly. .032 inch thick brass triple-wipe power contacts. Two drive screws anchor steel st |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00785007241662 |
| Manufacturers Part Number | TR20-BK |
| UPC | 785007241662 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 100 |
| Weight Per each | 0.2478 |

Uses, Certifications, and Standards

| | |
|--------------------------|--------------------------------------|
| Application | Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| nema rating | 5-20R |
| standard | CULUS, cULus UL498, CSA C22.2 No. 42 |