



## TAMPER-RESISTANT CONSTRUCTION SPEC GRADE SINGLE RECEPTACLES, BACK & SIDE WIRE, 20A, 125V, LIGHT ALMOND

TR5351LA | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Tamper-Resistant Construction Spec Grade Single Receptacle Back & Side Wire 20amp 125volt Light Almond

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Dual mechanical shutter system to help prevent insertions of foreign objects.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- .032 inch thick brass triple-wipe power contacts for lasting retention.
- Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuitwiring.
- Backed-out tri-drive steel terminal screws. Side wire capability.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Light Almond  
Type: Single Receptacles  
Number Of Poles: 2  
Number Of Wires: 3  
Special Features: Tamper-Resistant,back,side wire

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42  
CSA Standard: Yes  
Federal Spec: Yes  
UL Listing No: UL498  
UL Standard: Yes  
UN SPSC: 39121406  
UR: No

#### DIMENSIONS

Depth (US): 1.19"  
Height (US): 3.28"  
Width (US): 1.296"

#### TECHNICAL INFORMATION

Amps: 20A  
NEMA Configuration Number: 5-20R  
Volts: 125V  
Volts (AC): 125  
Capacity: Single  
Grade Type: Construction

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant





## TAMPER-RESISTANT CONSTRUCTION SPEC GRADE SINGLE RECEPTACLES, BACK & SIDE WIRE, 20A, 125V, LIGHT ALMOND

TR5351LA | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Tamper-Resistant Construction Spec Grade Single Receptacle Back & Side Wire 20amp 125volt Light Almond

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Dual mechanical shutter system to help prevent insertions of foreign objects.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- .032 inch thick brass triple-wipe power contacts for lasting retention.
- Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuitwiring.
- Backed-out tri-drive steel terminal screws. Side wire capability.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Light Almond  
Type: Single Receptacles  
Number Of Poles: 2  
Number Of Wires: 3  
Special Features: Tamper-Resistant,back,side wire

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42  
CSA Standard: Yes  
Federal Spec: Yes  
UL Listing No: UL498  
UL Standard: Yes  
UN SPSC: 39121406  
UR: No

#### DIMENSIONS

Depth (US): 1.19"  
Height (US): 3.28"  
Width (US): 1.296"

#### TECHNICAL INFORMATION

Amps: 20A  
NEMA Configuration Number: 5-20R  
Volts: 125V  
Volts (AC): 125  
Capacity: Single  
Grade Type: Construction

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

