



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR5362USBI Dup Rec 20A TR Spec W/3.1A Usb CHRG I

Pass & Seymour/Legrand

Catalog Number	TR5362USBI
Manufacturer	Pass & Seymour/Legrand
Description	Combination 20A 125V Tamper-Resistant Duplex Outlet With Two Usb Chargers - Ivory
Weight per unit	0.3392 (lbs/each)
Product Category	Combination Devices

Features

amperage rating	20
connection	Side & Back Wired
Dielectric Strength	Withstands 2000V minimum
Number of Wires	3
Phase	1
Poles	2
Voltage Rating	125
Wire Size	14 -10

Dimensions and Weight

Depth	1.392
Height	3.281
Width	1.693

Descriptions

Description	DUP REC 20A TR SPEC W/3.1A USB CHRG I
extra long description	P&S TR5362USBI DUP REC 20A TR SPEC
Long Description	Combination 20A 125V Tamper-Resistant Duplex Outlet with Two USB Chargers - Ivory
Product Type	Dup Rec 20A TR Spec W/3.1A Usb CHRG I
Special Features	Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007031584
Manufacturers Part Number	TR5362USBI
UPC	785007031584

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Tamper-Resistant USB Duplex Receptacle



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	50
Weight Per each	0.3392

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	UL94 V2
Mounting	BOX
nema rating	5-20R
standard	CSA Listed, cULus, FSUL, UL Listed, RoHS