



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR5362USBW Dup Rec 20A TR Spec W/3.1A Usb CHRG W

Pass & Seymour/Legrand

Catalog Number	TR5362USBW
Manufacturer	Pass & Seymour/Legrand
Description	Duplex Receptacle, 2 Poles, 20 A, 125 V, #14 to #10 Awg Wire Size, White, 3 Wires, Thermoplastic, 1.392 (D) X 1.693 (W) X 3.281 (H) In, Box Mount, -40 °C Operating Temperature, +60 °C Operating Temperature, 0.34 LB
Weight per unit	0.3392 (lbs/each)
Product Category	Combination Devices

Features

amperage rating	20
connection	Side & Back Wired
Dielectric Strength	Withstands 2000V minimum
Phase	1
Poles	2
Voltage Rating	125

Dimensions and Weight

Depth	1.392
Height	3.281
Width	1.693

Descriptions

Description	DUP REC 20A TR SPEC W/3.1A USB CHRG W
extra long description	P&S TR5362USBW DUP REC 20A TR SPEC

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007031669
UPC	785007031669

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
Type	Tamper-Resistant USB Duplex Receptacle

Packaging

Carton	10
Package	50
Weight Per each	0.3392



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	UL94 V2
Mounting	BOX
standard	CSA Listed, cULus, FSUL, UL Listed, RoHS