



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TR63GRY TR Recept 20A 125V Gy

*Pass & Seymour/Legrand*

Catalog Number	TR63GRY
Manufacturer	Pass & Seymour/Legrand
Description	Tamper-Resistant Spec Grade Receptacles, Back and Side Wire, 20A, 125V
Weight per unit	0.2515 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
media	Yes
Number of Wires	3
Outlet Type	Commercial, Indoor, Tamper-Resistant
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

### Material, Color, and Finish

Color	Gray
-------	------

### Dimensions and Weight

Height	3.281
Width	.900



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	TR RECP 20A 125V GY
extra long description	P&S TR63GRY TAMPR RESISTNT RECP 20A
Long Description	Tamper-Resistant Spec Grade Receptacles, Back and Side Wire, 20A, 125V
Product Type	Tampr Resistnt Recp 20A 125V Gry
Special Features	Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects. Exclusive patented feature, circuit label on face allows permanent circuit identification. Extra heavy-duty brass, one-piece mounting strap with integral ground. One-piece, brass, triple-wipe power contacts for lasting retention. Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Impact-resistant nylon face and back body. Easily accessed break-off, line-contact conne

## Manufacturer Information

Brand	Pass & Seymour/Legrand
GTIN	00785007268034
Manufacturers Part Number	TR63-GRY
UPC	785007268034

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	100
Weight Per each	0.2515

## Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	CULUS, FEDSPEC, UL498, CSA C22.2 No. 42
Temperature Rating	-40° - 60° C