



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR63W TR Recept 20A 125V WH

Pass & Seymour/Legrand

Catalog Number	TR63W
Manufacturer	Pass & Seymour/Legrand
Description	Tamper-Resistant Spec Grade Receptacles, Back and Side Wire, 20A, 125V
Weight per unit	0.2500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
media	Yes
Number of Wires	3
Outlet Type	Commercial, Tamper-Resistant, Indoor
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Material, Color, and Finish

Color	White
Finish	Matte

Dimensions and Weight

Height	3.281
Width	.900



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	TR RECP 20A 125V WH
extra long description	P&S TR63W TAMPER RESIST RECEP 20A 1
Long Description	Tamper-Resistant Spec Grade Receptacles, Back and Side Wire, 20A, 125V
Product Type	Tamper Resist Recep 20A 125V WH
Special Features	Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects. Exclusive patented feature, circuit label on face allows permanent circuit identification. Extra heavy-duty brass, one-piece mounting strap with integral ground. One-piece, brass, triple-wipe power contacts for lasting retention. Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Impact-resistant nylon face and back body. Easily accessed break-off, line-contact conne

Manufacturer Information

Brand	Pass & Seymour/Legrand
GTIN	00785007268027
Manufacturers Part Number	TR63-W
UPC	785007268027

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.25

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	CULUS, FEDSPEC, UL498, CSA C22.2 No. 42
Temperature Rating	-40° - 60° C