



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR7745WBOX 15A 125V WH 2PORT TR Usb Duplex Recp

Eaton Wiring Devices

| | |
|------------------|--|
| Catalog Number | TR7745WBOX |
| Manufacturer | Eaton Wiring Devices |
| Description | Combo 2 Port Usb Duplex Recp 15A 125V WH |
| Weight per unit | 0.3700 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|--------------|
| amperage rating | 15 A |
| connection | 4714 Lm |
| Dielectric Strength | 2000V |
| insulation | PC |
| Material | PC |
| Number of Wires | 3 in |
| Poles | 2 A |
| Voltage Rating | 125 A |
| Wire Size | 14 To 12 AWG |

Material, Color, and Finish

| | |
|-------|-------------|
| Color | WHITE GLOSS |
|-------|-------------|

Descriptions

| | |
|------------------|--|
| Description | 15A 125V WH 2PORT TR USB DUPLEX RECP |
| Long Description | COMBO 2 PORT USB DUPLEX RECP 15A 125V WH |
| Product Type | Combo 2 Port Usb Duplex Recp 15A 125V WH |
| Special Features | USB, duplex receptacle, wire leads |

Manufacturer Information

| | |
|---------------------------|----------------------|
| Brand | Eaton Wiring Devices |
| GTIN | 00032664731556 |
| Manufacturers Part Number | TR7745W-BOX |
| sub brand | Arrow Hart |
| UPC | 032664731556 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | Commercial receptacles |
| Type | DUPLEX |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.37 |

Uses, Certifications, and Standards

| | |
|--------------------------|---------------------|
| Application | Standard grade deco |
| environmental conditions | Indoor |
| Mounting | FLUSH |
| nema rating | 5-15R |
| standard | UL mA |
| Temperature Rating | -20 to 60 C |