

Specifications



Eaton TR7766BK-BOX

Eaton combination 3.6A USB charger with duplex receptacle, 20A, 125V, BK, FLUSH

General specifications

PRODUCT NAME	Eaton combination USB charger with duplex receptacle
CATALOG NUMBER	TR7766BK-BOX
UPC	032664767043
PRODUCT LENGTH/DEPTH	1.4 in
PRODUCT HEIGHT	4.19 in
PRODUCT WIDTH	1.3 in
PRODUCT WEIGHT	0.793 lb
CERTIFICATIONS	cULus Listed
PRODUCT TYPE	Combination USB charger with duplex receptacle



Powering Business Worldwide

Product specifications

TYPE	Type A
AMPERAGE RATING	20A
VOLTAGE RATING	125 V
CONTACT MATERIAL	Brass
FEATURES	Tamper resistant 3.6A Charging
WIRING METHOD	Screw terminals
NUMBER OF WIRES	Three-wire
MOUNTING METHOD	Flush
NUMBER OF POLES	Two-pole
PACKAGING TYPE	Retail Box
COLOR	Black
MATERIAL	Thermoplastic
STYLE	Decorator
ALLOWABLE WIRE SIZE	Side or Back Wiring :#10- 14 Copper or Copper Clad Aluminum
NEMA CONFIGURATION	5-20R
TORQUE RATING	14 lbf-inch
COMBINATION TYPE	USB
DESIGN TYPE	Receptacle
RECEPTACLE TYPE	Two-pole, three-wire, grounding

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Resources

BROCHURES	USB Duplex Receptacle Devices Brochure
MULTIMEDIA	Eaton's USB charging receptacles - Never miss a moment Introduction to USB-C Duplex Receptacles Fast and convenient charging made easy with Eaton's USB receptacles
SPECIFICATIONS AND DATASHEETS	Combination USB 3.6A charger with TR duplex receptacle Eaton Specification Sheet - TR7766BK-BOX



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

