



Powering Business Worldwide

pe.eaton.com

Arrow Hart Tamper Resistant Self-test GFCI Receptacle

TRSGF15W-3

UPC:032664742897

Dimensions:

- **Height:** 2.056 IN
- **Length:** 2.056 IN
- **Width:** 2.834 IN

Weight: .377 LB

Warranties: No Data

Specifications:

- **Special Features:** Qty. 3
- **Amperage Rating:** 15A
- **Voltage Rating:** 125V
- **Wiring Method:** Back wire and side wire
- **Circuit Interrupter Type:** GFCI
- **Color:** White
- **Contact Material:** Brass
- **Device Type:** Receptacle
- **Environmental Conditions:** Tamper resistant
- **Face/Body Material:** PVC
- **Nema Configuration:** 5-15R
- **Receptacle Type:** Two-pole, three-wire, grounding

Supporting documents: No Data

Certifications:

- NOM
- cULus Listed

Product compliance: No Data





Powering Business Worldwide

pe.eaton.com

Arrow Hart Tamper Resistant Self-test GFCI Receptacle

TRSGF15W-3

UPC:032664742897

Dimensions:

- **Height:** 2.056 IN
- **Length:** 2.056 IN
- **Width:** 2.834 IN

Weight: .377 LB

Warranties: No Data

Specifications:

- **Special Features:** Qty. 3
- **Amperage Rating:** 15A
- **Voltage Rating:** 125V
- **Wiring Method:** Back wire and side wire
- **Circuit Interrupter Type:** GFCI
- **Color:** White
- **Contact Material:** Brass
- **Device Type:** Receptacle
- **Environmental Conditions:** Tamper resistant
- **Face/Body Material:** PVC
- **Nema Configuration:** 5-15R
- **Receptacle Type:** Two-pole, three-wire, grounding

Supporting documents: No Data

Certifications:

- NOM
- cULus Listed

Product compliance: No Data

